

## SUMMER SAVINGS

### Cooling Products

#### PIP® Orange EZ-Cool® Max Nylon HyperKewl® Cooling Vest

Provides Several Hours of Cooling Relief. Durable, Lightweight, Active Fit, Vest Reduces Fatigue And Heat Stress. Sizes: M-3X.

PIP390-EZHYPCC-M/L/XL/2X/3X | Cooling Vest **\$144.95**  
 PIP390-HY099 | Cooling Packs, 4/Pack **\$94.95**



#### PIP® EZ-Cool® Max Cooling Sleeves

Nylon/Spandex Sleeve, UPF 40+ Blocks UV Rays. Sizes: M/L-XL/2X.

PIP391EZ275BKML/XL2XL | Black **\$4.95**  
 PIP391EZ275LYML/XL2XL | Yellow



#### RADNOR™ Blue PVA Evaporative Cooling Towel

13 in x 29.5 in (33 cm x 75 cm). Can Last For Up to 4 Hours on a Single Soak, Simply Re-Wet to Increase Cooling Duration.

● RAD64055500 **\$5.00**



#### RADNOR Hard Hat Terry Cloth Sweatband Liner

Fits Most Hard Hats And Safety Helmets.

RAD64055519 **\$2.50**



#### RADNOR Cotton/PVA Evaporative Cooling Bandana

Designed to Create a Feeling Colder Than The Ambient Air Temperature.

● RAD64055505 | Blue **\$3.50**  
 ● RAD64055506 | Lime



#### RADNOR FR Cotton Cooling Bandana

Remains Hydrated For Up to 4 Hours.

RAD64055517 | Blue **\$11.00**  
 RAD64055518 | Lime



### High-Vis Clothing

#### RADNOR Hi-Vis Yellow Polyester Mesh Vest

ANSI Type. Type R, Class 2. Sizes: L/XL & 2XL/3XL.

RAD64056636/7 **\$3.95**  
 RAD64056659/60



#### RADNOR Hi-Vis Yellow Polyester Mesh T-Shirt

ANSI Type. Type R, Class 2. Sizes: S-4XL.

RAD64056674-RAD64056680 **\$7.95**



### Head Protection

#### PIP® Hi-Vis Yellow Ranger Hat

Polyester, Full Brim Lightweight Hat With Mesh Crown Keeps Head Ventilated and Cool. ANSI Compliant Materials.

PIP350-RANGER **\$5.95**



#### PIP® Hi-Vis EZ-Cool® Sunshield

High Visibility Fabric and Silver Reflective Tape.

PIP396-800-YEL **\$7.95**  
 PIP396-850-LY **to \$9.95**  
 PIP396-851FR-LY



#### RADNOR by 3M™ SPEEDGLAS™ Welding Helmet

Compliant With ANSI Z87.1

- RAD64005280 | 10 sq in viewing area, Passive Helmet, Shade 10. **\$29.99**
- RAD64005244 | 6 sq in viewing area, Auto Darkening, 10-12 Variable Shades **\$99.99**
- RAD64005243 | 6 sq in viewing area, Auto Darkening, Variable Shades, 3, 8-12 & Grinding Mode. **\$149.99**
- RAD64005228 | 6 sq in viewing area, Auto Darkening, Variable Shades 4, 8-12, Lightweight design 12.6oz. **\$199.99**



### Hydration Products

#### SQWINCHER® Powder Pack Concentrate

Grape, Fruit Punch. 2.5 Gal Yield. 32/Packs.

KPG159016046/42 **\$108.25 to \$113.25**



#### SQWINCHER® Liquid Concentrate Bottle

Fruit Punch, Grape. 5 Gal Yield. 6 Per Case.

KPG159030322/25 **\$9.50**



#### SQWINCHER® Qwik Stik® Zero Powder Concentrate

Fruit Punch, Grape, Orange, Mixed Berry. 50/pk. 20oz Yield. Assorted, 4 tubes/case, 10/tube. 20oz Yield.

KPG159060100/01/02/07 **\$17.50**  
 KPG159060119 | Assorted **\$80.50**



⚠️ WARNING: Cancer and Reproductive Harm www.p65warnings.ca.gov



### RADNOR™ Premium Grade Pigskin/Split Cowhide Stick Welders Gloves

Black And Red Flames. Price Per Pair. Sizes: S-XL.

RAD64053425- **\$24.95**  
RAD64053428



### RADNOR Premium Grain Pigskin/Cowhide Pigskin MIG Welders Gloves

Black And Yellow. Price Per Pair. Sizes: S-2XL.

RAD64053435- **\$24.95**  
RAD64053439



### RADNOR Premium Grain Goatskin/Cowhide TIG Welders Gloves

Black And Yellow. Price Per Pair. Sizes: S-2XL.

RAD64053400- **\$22.95**  
RAD64053404



### RADNOR Premium Top Grain Kidskin Leather Unlined Welders Glove

White And Brown. Price Per Pair. Sizes: S-2XL.

RAD64056145- **\$14.95**  
RAD64056149



### RADNOR Kidskin Leather Cut Resistant Welders Gloves

TIG Welding Gloves. Price Per Pair. Sizes: S-2XL.

RAD64056140- **\$18.95**  
RAD64056144



**NEW!**

TOUCHSCREEN COMPATIBLE

### RADNOR Kyorene® 15 Gauge Graphene Fiber Cut Resistant Gloves

With Micro-Foam Nitrile Coated Palm And Knit Wrist Cuff. ANSI A6 Cut Protection. Price Per Pair. Sizes: XS-2XL.

RAD64056340- **\$8.95**  
RAD64056345



**NEW!**

### RADNOR 13 Gauge High Performance Polyethylene Cut Resistant Gloves

ANSI Cut Level A5, Polyurethane Coated Palm And Fingers. Price Per Pair. Sizes: S-XL.

⚡ RAD64053495- **\$6.95**  
⚡ RAD64053498



### RADNOR 13 Gauge Polyethylene Cut Resistant Gloves

ANSI Cut Level A2, Polyurethane Coated Palm And Fingers. Price Per Pair. Sizes: S-2XL.

RAD64056926- **\$4.75**  
RAD64056930

## RADNOR by AngelFire® Women's Welding PPE

DESIGNED SPECIFICALLY FOR WOMEN

### RADNOR by AngelFire® Women's FR Cotton Welding Jacket

Flame Resistant, With Snap Front Closure And 3-Position Waist Adjustment Strap. Sizes: XS-XL.

RAD64053415- **\$32.95**  
RAD64053419



### RADNOR by AngelFire® Women's FR Hybrid Welding Jacket

Flame Resistant, With Snap Front Closure And 3-Position Waist Adjustment Strap. Sizes: XS-XL.

RAD64053420- **\$64.95**  
RAD64053424



## Welding Jacket



### RADNOR by BSX® FR Flame Resistant Welding Jacket

With Snap Front Closure And 2-Position Waist Adjustment Strap, Extended Cuff. The Iconic Black With Red Flame Design Adds a Touch of Personality Without Compromising on Durability or Function. Sizes: S-3XL.

RAD64053429- **\$32.95**  
RAD64053434

### RADNOR by AngelFire® Women's Premium Pigskin Palm Stick Glove

Expertly Designed to Fit a Woman's Hand. Price Per Pair. Sizes: XS-L.

RAD64053405- **\$39.95**  
RAD64053408



### RADNOR by AngelFire® Women's Premium Kidskin & FR Cotton TIG Glove

Expertly Designed to Fit a Woman's Hand. Price Per Pair. Sizes: S-XL.

RAD64053411- **\$29.95**  
RAD64053414



⚠️ WARNING: Cancer and Reproductive Harm www.p65warnings.ca.gov



## RADNOR™ ER4043 Aluminum MIG Wire or TIG ROD

Gas Recommendation of ARCAL™ Prime.  
Approvals: AWS A5.10/A510.M, CWB/CSA W48-0.



PART #	DESCRIPTION	PRICE
<b>MIG Wire</b>		
Diameters Available: .030" (0.8 mm), .035" (0.9 mm), 3/64" (1.2mm), 1/16" (1.6mm)		
Packaging Available: 1 lb. Spool, 16 lb. Spool, 60 lb. Mini Drum, 300 lb. RADNOR Gem-Pak®		
<b>NEW!</b> ⚡ RAD64001470/1/2/3 ⚡ RAD64001500/2/4/8/10/11 ⚡ RAD64001525/26/27		<b>Call For Price</b>
<b>TIG ROD</b>		
Diameters Available: 1/16" (1.6 mm), 3/32" (2.4 mm) 1/8" (3.2 mm)		
Packaging Available: 1 lb. Tube, 10 lb. Carton		
<b>NEW!</b> ⚡ RAD64001478/79/80 ⚡ RAD64001594/95/96		<b>Call For Price</b>

## RADNOR ER5356 Aluminum MIG Wire or TIG ROD

Gas Recommendation of ARCAL™ Prime.  
Approvals: AWS A5.10/A510.M, CWB/CSA W48-0.



PART #	DESCRIPTION	PRICE
<b>MIG Wire</b>		
Diameters Available: .030" (0.8 mm), .035" (0.9 mm), 3/64" (1.2mm), 1/16" (1.6mm)		
Packaging Available: 1 lb. Spool, 16 lb. Spool, 60 lb. Mini Drum, 300 lb. RADNOR Gem-Pak®		
<b>NEW!</b> ⚡ RAD64001474/5/6/7 ⚡ RAD64001512/14/16/ 20/22/23 ⚡ RAD64001529/30/31		<b>Call For Price</b>
<b>TIG ROD</b>		
Diameters Available: 1/16" (1.6 mm), 3/32" (2.4 mm) 1/8" (3.2 mm)		
Packaging Available: 1 lb. Tube, 10 lb. Carton		
<b>NEW!</b> ⚡ RAD64001481/82/83 ⚡ RAD64001597/98/99		<b>Call For Price</b>

## Face Protection & Accessories

### RADNOR Faceshields



Assorted Sizes & Shield Colors.

PART #	DESCRIPTION	PRICE
⚡ RAD64051709	Mesh/Steel, Gray, Each. 9x15.5x.04"	<b>\$6.75</b>
⚡ RAD64051710 /40	Polycarbonate, Clear, .06" Each or 50/Case. 8x15.5" or 9x15.5"	<b>\$5.50 TO \$10.00</b>
⚡ RAD64051720 /30/50	Propionate, Clear, .06" Each or 50/Case. 8x16.5" / 9x15.5" / 9.75x19"	<b>\$5.75 TO \$8.25</b>
⚡ RAD64051722 /32/52	Polycarbonate, Dark Green, .06", 50/Case. 8x16.5" / 9x15.5" / 9.75x19"	<b>\$5.75 TO \$10.00</b>
⚡ RAD64051723 /33/53	Polycarbonate, Green Shade 3, .06", 50/Case. 8x16.5" / 9x15.5" / 9.75x19"	<b>\$18.75 TO \$22.00</b>
⚡ RAD64051725 /35/55	Polycarbonate, Green Shade 5, .06", Each or 50/Case. 8x16.5" / 9x15.5" / 9.75x19"	<b>\$17.50 TO \$20.00</b>

### RADNOR Mounting Brackets For Hard Hats & Headgear



Aluminum, Plastic, Rubberband, Full Brim Hat Options.

⚡ RAD64051065/66/67/68/76

**\$3.50 TO \$12.25**

### RADNOR Safety Glasses



Blue Hard Coat/Mirror, Anti-Fog, Anti-Scratch, Clear, Polarized Over The Glasses Lens Options. Price Per Pair.

RAD64051265/68  
RAD64051541/46  
RAD64051654/57/58/59

**\$3.25 TO \$22.50**

### PIP® Site Boss™ Safety Glasses



Mirror Plus™ Pro Lens. Price Per Pair.

PIP250-43-0008 | White  
PIP250-43-0006 | Orange

**\$10.75**

## Welding & Plasma Cutting Machines

### RADNOR 45A Plasma Cutter w/ Handheld Torch



⚡ RAD64000050 **\$2,374.99**

### LINCOLN ELECTRIC® Power MIG® 262P Pulsed MIG Welder



⚡ LINK5378-1 **Call For Price**

### LINCOLN ELECTRIC® Power MIG® 262MP Multi-Process Welder Aluminum One-Pak®



⚡ LINK5637-1 **Call For Price**

## Welder's Caps

### RADNOR ASSORTED COLORS COTTON WELDER'S CAPS



⚡ RAD64056110 | Non-Reversible **\$7.95**  
⚡ RAD64056111 | Reversible **\$8.95**

## First Aid Cabinets and Kits

### Acme-United Corporation First Aid Kit



Heat Stress First Aid Kit . White Plastic, Portable/Wall Mount 25 Person.

AU35250 **\$27.75**

**NEW!**

### RADNOR First Aid Cabinets or Kits



Personal & Contractor. Portable Or Wall Mount. Meets ANSI standards. Metal or Plastic.

RAD64058062

RAD64058053 | 25 person, Plastic, Kit **\$28.75**  
RAD64058062 | 150-200 Person, Metal, Cab. **\$272.75**  
RAD64058095 | Bloodborne Pathogen Spill Kit **\$33.75**

⚠️ WARNING: Cancer and Reproductive Harm www.p65warnings.ca.gov



## MAKITA® Corded Grinder



PART #	DESCRIPTION	PRICE
MAKGA4530X	115 V/ 6 Amp 4 1/2", Small Angle Grinder w/5 Grinding Wheels	\$99.25
MAKGA5052	115 Volts/11 Amp 4.5" - 5", Small Angle Grinder	\$129.00
MAKGD0601	25,000 RPM 3.5 Amp 1/4" Die Grinder	\$177.75
MAKGA6010Z	115 V/10.5 Amp 6", Small Angle Grinder	\$232.75
MAK9005B	115 V/ 6 Amp 4 1/2", Small Angle Grinder	\$244.00

## Air/Fuel Torches

### RADNOR™ Target Torch™ Torch Kit



Air/Acetylene 12" x 17.5". Adjustable Target Tips For Professional Soldering And Brazing Applications.

● RAD64004591 **\$268.25**

### RADNOR TX-504 Hand Torch



1.8" X 6.89" X 13.75" MAP-Pro/LP Gas Heating/Brazing/Soldering Hand Torch.

RAD64004584 **\$120.50**

### RADNOR 35" Propane Weed Burning/Melting/Drying Torch Kit

Professional Heavy Duty. No Smoke, No Fumes. Durable 10 Ft. Neoprene Hose, Accurate Brass Flow Control Shut-Off Valve, Brass Propane Tank Adapter, Spark Igniter. Applications: Weed Burning, Melting, Drying. CGA Connection 510.

● RAD64003888 **\$130.50**



## Welding Support Equipment

### LINCOLN ELECTRIC® Contact Tip For Magnum® PRO MIG Guns

Copper Plus® Contact Tip - 550A, Aluminum, Tapered, 10/pack.

● LINKP2745-035AT | .035 in (0.9 mm) **\$5.50**

● LINKP2745-364AT | 3/64 in (1.2 mm) **\$5.75**



### LINCOLN ELECTRIC® Magnum® Pro AL FC 225 Air-Cooled Push-Pull Guns

225 Amp, 12 Pin Style Connector, 25' Cable.

● LINK4797-2 **\$4,801.75**



### LINCOLN ELECTRIC® Accu-Pak® Payoff Kit, 24"

Polyethylene Box. Includes Direct Pull Kit.

● LINK2175-2 **\$438.00**



## RADNOR by Flextur™

### Welding Fixture Tables

Available in a Variety of Sizes & Configurations.



PART #	DESCRIPTION	PRICE
5-SIDED STATIONARY TABLES		
● RAD64008962	Bare Steel   48"x48" Stationary Welding Table	\$4,370.00
● RAD64008963	Nitride+   48"x48" Stationary Welding Table	\$5,367.50
● RAD64008966	Bare Steel   96"x48" Stationary Welding Table	\$7,552.50
● RAD64008967	Nitride+   96"x48" Stationary Welding Table	\$9,310.00

STATIONARY TABLES & FIXTURE KITS		
● RAD64008958	Bare Steel   36"x30" Stationary Welding Table	\$1,757.50
● RAD64008959	Nitride+   36"x30" Stationary Welding Table	\$2,090.00
● RAD64008950	Bare Steel   36"x30" Stationary Welding Table & Fixture Kit <sup>1</sup>	\$2,565.00
● RAD64008951	Nitride+   36"x30" Stationary Welding Table & Fixture Kit <sup>1</sup>	\$2,992.50
● RAD64008960	Bare Steel   72"x36" Stationary Welding Table	\$3,420.00
● RAD64008961	Nitride+   72"x36" Stationary Welding Table	\$3,990.00
● RAD64008952	Bare Steel   72"x36" Stationary Welding Table & Fixture Kit <sup>1</sup>	\$4,132.50
● RAD64008953	Nitride+   72"x36" Stationary Welding Table & Fixture Kit <sup>1</sup>	\$4,702.50

5-SIDED MOBILE TABLES & FIXTURE KITS		
● RAD64008964	Bare Steel   48"x48" Mobile Welding Table	\$4,845.00
● RAD64008965	Nitride+   48"x48" Mobile Welding Table	\$5,605.00
● RAD64008954	Bare Steel   48"x48" Mobile Welding Table & Fixture Kit <sup>3</sup>	\$6,745.00
● RAD64008955	Nitride+   48"x48" Mobile Welding Table & Fixture Kit <sup>3</sup>	\$7,505.00
● RAD64008968	Bare Steel   96"x48" Mobile Welding Table	\$8,217.50
● RAD64008969	Nitride+   96"x48" Mobile Welding Table	\$9,975.00
● RAD64008956	Bare Steel   96"x48" Mobile Welding Table & Fixture Kit <sup>2</sup>	\$12,777.50
● RAD64008957	Nitride+   96"x48" Mobile Welding Table & Fixture Kit <sup>2</sup>	\$14,535.00

MOBILE WELDING CARTS & FIXTURE KITS		
● RAD64008971	Bare Steel   48"x30" Mobile Welding Cart	\$2,367.40
● RAD64008973	Nitride+   48"x30" Mobile Welding Cart	\$3,004.85
● RAD64008970	Bare Steel   48"x30" Mobile Welding Cart & Fixture Kit <sup>4</sup>	\$3,160.65
● RAD64008972	Nitride+   48"x30" Mobile Welding Cart & Fixture Kit <sup>4</sup>	\$3,607.15

FIXTURE KITS (COMPATIBLE WITH ALL RADNOR WELDING TABLES)		
● RAD64008974	Steel   27 Piece Fixture Kit	\$845.50
● RAD64008975	Steel   57 Piece Fixture Kit	\$1,995.00
● RAD64008976	Steel   95 Piece Fixture Kit	\$5,172.75

<sup>1</sup> 27 Piece Fixture Kit | <sup>2</sup> 95 Piece Fixture Kit | <sup>3</sup> 57 Piece Fixture Kit | <sup>4</sup> 40 Piece Fixture Kit

### LINCOLN ELECTRIC® Magnum® Pro AL FC 225 Air-Cooled Push-Pull Guns

225 Amp, 12 Pin Style Connector, 25' Cable.

● LINK4797-2 **\$4,801.75**



### LINCOLN ELECTRIC® Accu-Pak® Payoff Kit, 24"

Polyethylene Box. Includes Direct Pull Kit.

● LINK2175-2 **\$438.00**



### LINCOLN ELECTRIC® Accu-Trak® Drum Payoff Kit, 20"

Polyethylene Wire Delivery Cone.

● LINK884-5 **\$443.75**



### LINCOLN ELECTRIC® Drive Roll and Wire Guide Kit

For Use With .035 in (0.9 mm) Aluminum Wire.

● LINKP1695-035A **\$328.50**



⚠️ WARNING: Cancer and Reproductive Harm www.p65warnings.ca.gov