

Airgas®

an Air Liquide company

RADNOR™ by 3M™ Speedglas™ Helmet Closeout Sale - Save up to 60%

Welding Helmets & Welding Helmet Accessories

RS-70 Black/
Gray Fixed Front
Welding Helmet
W/3.76" X 2.65"
Shade 10 Lens



NOW \$29.99

[RAD64005280](#)

RS-500 Black
Welding Helmet
W/3.66" X 1.73"
Variable Shades 2,
10-12 Auto
Darkening Lens



NOW \$99.99

[RAD64005244](#)

RS-700 Black/
Gray Welding
Helmet W/3.66"
X 1.73" Variable
Shades 4, 8-12 Auto
Darkening Lens



NOW \$149.99

[RAD64005243](#)

RS-900 Black/
Gray Welding
Helmet W/4.21"
X 2.17" Variable
Shades 8-12 Auto
Darkening Lens



NOW \$199.99

[RAD64005228](#)

RS-Superlight
Black/Gray Welding
Helmet W/3.57"
X 1.68" Variable
Shades 4, 8-12 Auto
Darkening Lens



NOW \$219.99

[RAD64005261](#)

Hardhat Adapter
For RS-900/RS-
700/RS-500/RS-
70 Welding
Helmet



NOW \$35.62

[RAD64005241](#)

RS-900 RS-700
RS-500 1.5
Diopter Clear
Polycarbonate
Magnifying Lens



NOW \$22.19

[RAD64005236](#)

RS-900 RS-700
RS-500 2.0
Diopter Clear
Polycarbonate
Magnifying Lens



NOW \$22.19

[RAD64005237](#)

RS-900 RS-700
RS-500 2.5
Diopter Clear
Polycarbonate
Magnifying Lens



NOW \$24.09

[RAD64005238](#)

RS-900 RS-700
RS-500 3.0
Diopter Clear
Polycarbonate
Magnifying Lens



NOW \$24.09

[RAD64005239](#)

Fill Your Potential.™

Contact your local Airgas sales representative or local Airgas branch for more information.

Sale pricing* valid now through 6/30/2026 or while supplies last.

*Pricing available only to customers serviced by Airgas East. If using Airgas.com, login is required to receive promotional pricing. Existing customers may contact Airgas at us-eastpromo@airgas.com if you find that the promotional pricing is not applied to your account. See www.airgas.com/east-restrictions for additional rules. Pricing subject to change as affected by tariffs.

855.636.6316 | Airgas.com